

Crop Dryer Motors

Model No: 284TTFCD6327

Catalog No: Y019

Crop Dryer Motor, 25 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 284TZ Frame, TEFC

Product Information Packet: Model No: 284TTFC6327, Catalog No: Y019 Crop Dryer Motor, 25 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 284TZ Frame, TEFC

Nameplate Specifications

Phase	3	Output HP	25 Hp
Output KW	18.7 kW	Voltage	230/460 V
Speed	1772 r/min	Synchronous RPM	1800 r/min
Service Factor	1.15	Frame	284TZ
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	Thermostat
Efficiency	93.6 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	60.0/30.0 A
Power Factor	83	Duty	Continuous
Insulation Class	H	Design Code	B
KVA Code	G	Drive End Bearing Size	6311
Opp Drive End Bearing Size	6211	UL	Recognized
CSA	Y	CE	Y
IP Code	55	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.2988 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1/F2 Capable
Inverter Load	Constant 10:1/Variable 10:1		

Drawings

Connection Drawing	EE7308T	Outline Drawing	SS621289-100
--------------------	----------------	-----------------	---------------------