

Elevator Duty Motors

Model No: 326TTDBD7026

Catalog No: GTE4055

Elevator Duty Motor, 50 & 60 HP, 3 Ph, 60 & 60 Hz, 230/460 & 230/460 V, 1800 RPM, 326T Frame, DP

Product Information Packet: Model No: 326TTDBD7026, Catalog No: GTE4055 Elevator Duty Motor, 50 & 60 HP, 3 Ph, 60 & 60 Hz, 230/460 & 230/460 V, 1800 RPM, 326T Frame, DP

Nameplate Specifications

Phase	3	Output HP	50 & 60 Hp
Output KW	37.0 & 45.0 kW	Voltage	230/460 & 230/460 V
Speed	1780 & 1780 r/min	Synchronous RPM	1800 & 1800 r/min
Service Factor	1.00 & 1.00	Frame	326T
Enclosure	Drip Proof	Thermal Protection	No Protection
Efficiency	94.5 & 94 %	Ambient Temperature	40 °C
Frequency	60 & 60 Hz	Current	118/59 & 138/69 A
Power Factor	84	Duty	120/80 Starts/Hour
Insulation Class	F	Design Code	B
KVA Code	G	Drive End Bearing Size	6312
Opp Drive End Bearing Size	6311	UL	Recognized
CSA	Y	CE	Y
IP Code	22	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Wye Start Delta Run
Poles	4	Rotation	Reversible
Resistance Main	.158 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1/F2 Capable

Drawings

Connection Drawing	EE7358	Outline Drawing	SS620746-200
--------------------	--------	-----------------	--------------