marathon®

# General Purpose Motors

**Model No:** 182TTDBD6000
**Catalog No:** GT0812

General Purpose Motor, 5 HP, 3 Ph, 60 Hz, 200 V, 3600 RPM, 182T Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

# Product Information Packet: Model No: 182TTDBD6000, Catalog No: GT0812 General Purpose Motor, 5 HP, 3 Ph, 60 Hz, 200 V, 3600 RPM, 182T Frame, DP

## Nameplate Specifications

| | | | |
|---|---|---|---|
| Phase | **3** | Output HP | **5 Hp** |
| Output KW | **3.7 kW** | Voltage | **200 V** |
| Speed | **3510 r/min** | Synchronous RPM | **3600 r/min** |
| Service Factor | **1.15** | Frame | **182T** |
| Enclosure | **Drip Proof** | Thermal Protection | **No Protection** |
| Efficiency | **86.5 %** | Ambient Temperature | **40 °C** |
| Frequency | **60 Hz** | Current | **15.2 A** |
| Power Factor | **82** | Duty | **Continuous** |
| Insulation Class | **F** | Design Code | **A** |
| KVA Code | **K** | Drive End Bearing Size | **6206** |
| Opp Drive End Bearing Size | **6203** | UL | **Recognized** |
| CSA | **Y** | CE | **Y** |
| IP Code | **22** | Number of Speeds | **1** |

## Technical Specifications


| | | | |
|---|---|---|---|
| Electrical Type | **Squirrel Cage Inverter Rated** | Starting Method | **Line Or Inverter** |
| Poles | **2** | Rotation | **Reversible** |
| Resistance Main | **4.05 O** | Mounting | **Rigid Base** |
| Motor Orientation | **Horizontal** | Drive End Bearing | **Ball** |
| Opp Drive End Bearing | **Ball** | Frame Material | **Rolled Steel** |
| Shaft Type | **T** | Assembly/Box Mounting | **F1/F2 Capable** |
| Inverter Load | **Constant 2:1/Variable 10:1** | | |


## Drawings


| | | | |
|---|---|---|---|
| Connection Drawing | **EE7300** | Outline Drawing | **SS600198-100** |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 14/10/2026

| DASH NO. | B | C | E | 2E | 2F | 2FF | BA | BS | MOUNTING | FRAME |
|---|---|---|---|---|---|---|---|---|---|---|
| 100 | 6.50 | 12.25 | 3.75 | 7.50 | 4.50 | 5.50 | 2.75 | 4.15 | F1 OR F2 | 182T |
| 200 | | 13.25 | | | | | | 5.15 | | 184T |




| DRAWING REVISION | REVISION BY | REV DATE/© DATE |
|---|---|---|
| G | SB | 08/11/2025 |
| REQUEST NUMBER | APPROVED BY | DATE |
| CR-0023556 | SBD | 08/11/2025 |

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

| | |
|---|---|
| DRAWN BY | PRIYA |
| DATE | 12/03/2018 |
| APPROVED BY | SBD |
| DATE | 12/03/2018 |
| REFERENCE | |
| THIRD ANGLE PROJECTION | |

marathon™

DESCRIPTION
OUTLINE
182/184T FR -NEMA-ODP RS


| MATERIAL | PROCESS/FINISH |
|---|---|
| | |

| SIZE | DRAWING NUMBER | SHEET |
|---|---|---|
| B | SS600198 | 1 OF 1 |

THREE PHASE - SINGLE VOLTAGE
MOTOR - CONDUIT BOX @ 'A'

TO REVERSE ROTATION:
INTERCHANGE ANY TWO LINE
LEAD CONNECTIONS

TERMINAL BLOCK WHEN SPECIFIED









VIEW OF TERMINAL END

IF MOTOR HAS
9 LEADS




IF MOTOR HAS
6 LEADS




A-9806 DECAL

OPTIONAL CORD
CONNECTION

| | |
|---|---|
| L1 | WHITE |
| L2 | RED |
| L3 | BLACK |

| | | |
|---|---|---|
| DRAWING REVISION: AD | REVISION BY: SB | REV DATE/© DATE: 08/01/2025 |
| REQUEST NUMBER: CR-0023654 | APPROVED BY: SBD | DATE: 08/01/2025 |

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

| | |
|---|---|
| DRAWN BY: DA | |
| DATE: 03-26-1993 | |
| APPROVED BY: TB | |
| DATE: 03-26-1993 | |
| REFERENCE | |
| THIRD ANGLE PROJECTION | |

marathon™

DESCRIPTION
CONNECTION DIAGRAM
EXTERNAL - SINGLE VOLTAGE - 3Ø MOTOR

| MATERIAL | PROCESS/FINISH |
|---|---|

| SIZE | DRAWING NUMBER | SHEET |
|---|---|---|
| A | EE7300 | 1 OF 1 |