marathon®

General Purpose Motors

Model No: 182TTFHD6101
Catalog No: GT72101

General Purpose Motor, 1 & 1 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 900 RPM, 182TC Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 182TTFHD6101, Catalog No: GT72101 General Purpose Motor, 1 & 1 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 900 RPM, 182TC Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**1 & 1 Hp**
Output KW	**0.75 & 0.75 kW**	Voltage	**230/460 & 190/380 V**
Speed	**875 & 712 r/min**	Synchronous RPM	**900 & 750 r/min**
Service Factor	**1.15 & 1.15**	Frame	**182TC**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**75.5 & 75.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**4/2 & 4.4/2.2 A**
Power Factor	**61.2**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**M**	Drive End Bearing Size	**6206**
Opp Drive End Bearing Size	**6205**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**8**	Rotation	**Reversible**
Resistance Main	**17.0269 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Aluminum**
Shaft Type	**T**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 10:1/Variable 10:1**		


Drawings


Connection Drawing	**EE7308**	Outline Drawing	**SS621248-100**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	AG	AH	BA	BV	MOUNTING	FRAME
100	5.67	15.83	4.50	3.75	7.50	-	4.50	13.20	2.62	3.50	5.87	F1 OR F2	182TC
200	6.69	16.83				4.50	5.50	14.20			6.37		182/184TC







DRAWING REVISION	REVISION BY	REV DATE/© DATE
C	SV	09/02/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0027530	RMS	09/02/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY	BISWA
DATE	18/01/2022
APPROVED BY	SBD
DATE	18/01/2022
REFERENCE	

marathon™

DESCRIPTION
OUTLINE
182/184TC FR-NEMA TEFC-AL FRAME

MATERIAL | PROCESS/FINISH

THIRD ANGLE PROJECTION

SIZE	DRAWING NUMBER	SHEET
B	SS621248	1 OF 1