marathon®

50 Hz Motors

Model No: 254TTDBD8026
Catalog No: H957A

50 Hz Motor, 15 HP, 3 Ph, 50 Hz, 200/400 V, 1500 RPM, 254T Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 254TTDBD8026, Catalog No: H957A 50 Hz Motor, 15 HP, 3 Ph, 50 Hz, 200/400 V, 1500 RPM, 254T Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**15 Hp**
Output KW	**11.2 kW**	Voltage	**200/400 V**
Speed	**1470 r/min**	Synchronous RPM	**1500 r/min**
Service Factor	**1.15**	Frame	**254T**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**88.5 %**	Ambient Temperature	**40 °C**
Frequency	**50 Hz**	Current	**42.0/20.9 A**
Power Factor	**84.8**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**F**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6208**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications

Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Part Wdg Start Low Volt Only & Wye Start Delta Run**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.604 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**T**	Assembly/Box Mounting	**F1/F2 Capable**

Drawings

Connection Drawing	**EE7358**	Outline Drawing	**SS620685-100**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 15/10/2026