marathon®

Fire Pump Motors

Model No: 404TSTDCD4332
Catalog No: U528A

Fire Pump Motor, 100 & 75 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 404TS Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 404TSTDCD4332, Catalog No: U528A Fire Pump Motor, 100 & 75 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 404TS Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**100 & 75 Hp**
Output KW	**75.0 & 56.0 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1785 & 1485 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**404TS**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**94.1 & 93.6 %**	Ambient Temperature	**50 °C**
Frequency	**60 & 50 Hz**	Current	**228/114 & 210/105 A**
Power Factor	**87**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**F**	Drive End Bearing Size	**6316**
Opp Drive End Bearing Size	**6315**	UL	**Listed**
CSA	**Y**	CE	**Y**
IP Code	**23**	Number of Speeds	**1**

Technical Specifications

Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Part Wdg Start Low Volt Only & Wye Start Delta Run**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.086 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**TS**	Overall Length	**33.86 in**
Frame Length	**19.68 in**	Shaft Diameter	**2 1/8 in**
Shaft Extension	**4.25 in**	Assembly/Box Mounting	**F1/F2 Capable**

Drawings

Connection Drawing	**EE7308AA**	Outline Drawing	**SS620752-404TS**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026