marathon®

Severe Duty Motors

Model No: 184THFCD9002
Catalog No: W523A-P

Severe Duty Motor, 5 HP, 3 Ph, 60 Hz, 460 V, 3600 RPM, 184T Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 184THFCD9002, Catalog No: W523A-P Severe Duty Motor, 5 HP, 3 Ph, 60 Hz, 460 V, 3600 RPM, 184T Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**5 Hp**
Output KW	**3.7 kW**	Voltage	**460 V**
Speed	**3510 r/min**	Synchronous RPM	**3600 r/min**
Service Factor	**1.15**	Frame	**184T**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**88.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**6.0 A**
Power Factor	**88**	Duty	**Continuous**
Insulation Class	**H**	Design Code	**B**
KVA Code	**J**	Drive End Bearing Size	**6206**
Opp Drive End Bearing Size	**6205**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**56**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**2**	Rotation	**Reversible**
Resistance Main	**3.55 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**T**	Shaft Diameter	**1.125 in**
Assembly/Box Mounting	**F1/F2 Capable**	Inverter Load	**Constant 2:1/Variable 10:1**


Drawings

Connection Drawing	**EE7300**	Outline Drawing	**SS600210-200**


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 14/10/2026

DASH NO.	B	C	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME
100	5.67	15.20	3.75	7.50	-	4.50	2.75	2.35	F1 OR F2	182T
200	6.69	16.20			4.50	5.50		2.75	F1 OR F2	182/184T





F2 VIEW



DRAWING REVISION: E	REVISION BY: SB	REV DATE/© DATE: 07/24/2025
REQUEST NUMBER: CR-0023556	APPROVED BY: SBD	DATE: 07/24/2025
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: BISWA	marathon™	
DATE: 24/12/2018	DESCRIPTION: OUTLINE 182/184T FR-NEMA-SD & IEEE841	
APPROVED BY: SBD		
DATE: 24/12/2018		
REFERENCE	MATERIAL	PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: B / DRAWING NUMBER: SS600210	SHEET: 1 OF 1

THREE PHASE - SINGLE VOLTAGE
MOTOR - CONDUIT BOX @ 'A'


TO REVERSE ROTATION:
INTERCHANGE ANY TWO LINE
LEAD CONNECTIONS

TERMINAL BLOCK WHEN SPECIFIED




VIEW OF TERMINAL END

IF MOTOR HAS
9 LEADS



IF MOTOR HAS
6 LEADS



A-9806 DECAL

OPTIONAL CORD
CONNECTION

L1	WHITE
L2	RED
L3	BLACK

DRAWING REVISION: AD	REVISION BY: SB	REV DATE/© DATE: 08/01/2025
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: DA	
DATE: 03-26-1993	
APPROVED BY: TB	
DATE: 03-26-1993	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
CONNECTION DIAGRAM
EXTERNAL - SINGLE VOLTAGE - 3Ø MOTOR

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	EE7300	1 OF 1

Data Sheet

Date: 9/14/2022
Customer:
Attention:
Submitted by:

marathon® Motors

184THFCD9002

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	2.30	2.80	3.6	4.8	6.0	6.9	7.5	45.0	
Torque (ft-lb)	0.00	1.85	3.7	5.6	7.5	8.6	9.4	14.0	
RPM	3600	3580	3555	3535	3510	3,500	3490	0	
Efficiency (%)		81.5	87.5	88.5	88.5	87.5	86.5		
P.F. (%)	9.0	52.0	73.0	83.0	88.0	89.0	90.0	50.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	1800	3000	3510	3600
Current (Amps)	45.0	38.0	28.0	6.0	2.30
Torque (ft-lb)	14.0	12.5	25.0	7.5	0.00



Information Block

HP	5.0	
Sync. RPM	3600	
Frame	184	
Enclosure	TEFC	
Construction	TFC	
Voltage	460	V
Frequency	60	Hz
Design	B	
LR Code letter	J	
Service Factor	1.15	
Temp Rise @ FL	45	° C
Duty	CONT	
Ambient	40	° C
Elevation	3,300	feet
Rotor/Shaft wk²	0.23	Lb-Ft²
Ref Wdg	HA31122016 R2	
Sound Pressure @ 1M	70	dBA
VFD Rating	CONSTANT 2:1/VARIABLE 10:1	
Outline Dwg		
Conn. Diag	EE7300	

Additional Specifications:

0

0

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
2.0980	1.0210	3.9690	1.5880	112.3790

Speed -Torque Curve

