marathon®

Close-Coupled Pump Motors

Model No: 213TTDWD16347
Catalog No: E167A

Close-Coupled Pump Motor, 7.50 HP, 3 Ph, 60 Hz, 200 V, 1800 RPM, 213JMV Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 213TTDWD16347, Catalog No: E167A Close-Coupled Pump Motor, 7.50 HP, 3 Ph, 60 Hz, 200 V, 1800 RPM, 213JMV Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**7.50 Hp**
Output KW	**5.6 kW**	Voltage	**200 V**
Speed	**1765 r/min**	Synchronous RPM	**1800 r/min**
Service Factor	**1.15**	Frame	**213JMV**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**91 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**23.0 A**
Power Factor	**77.1**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**H**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**1.56 O**	Mounting	**Round**
Motor Orientation	**Shaft Down**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**JM**	Overall Length	**18.94 in**
Shaft Diameter	**1 3/8 in**	Shaft Extension	**4.28 in**
Assembly/Box Mounting	**F1/F2 Capable**		

Drawings

Connection Drawing	**005102.01**	Outline Drawing	**SS86596-1115**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 15/10/2026

Uncontrolled Copy



DASH	FR.	C	AG	BV	
965	213JM	18.94	14.69	9.93	
1115	213/15JM	20.44	16.19	11.43	
1240	213/15JM	21.69	17.44	12.68	

NOTES:
1. NAMEPLATE TO BE READ FROM SHAFT EXT. END OF MOTOR.
2. BOX CAN BE MOUNTED IN 90° STEPS.

DRAWING REVISION	REVISION BY	REV DATE/ © DATE
J	SB	05/18/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026308	RMS	05/18/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	


REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45 °
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 INCH / 5.1 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	DESCRIPTION
DA	OUTLINE
DATE	210JM FR. - DR. PR. - C'FACE
03/26/1996	
APPROVED BY	
DN	
DATE	
04/01/1996	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: SS86596 / SHEET: 1 OF 1


marathon™

Uncontrolled Copy

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



LINE LEADS



CONNECT LEADS AS FOLLOWS
FOR FOUR CONDUCTOR CORD ( )

CORD	L1 (RED)	L2 (WHITE)	L3 (BLACK)	(GREEN)
MOTOR	T1	T2	T3	GROUND

DRAWING REVISION: L	REVISION BY: SV	REV DATE/ © DATE: 05/12/2026
REQUEST NUMBER: CR-0026249	APPROVED BY: RMS	DATE: 05/12/2026

REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED.
PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±0.5°
.XX	±0.01	[±0.3]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45 °
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: INCH 125 / mm 3.2 /
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY: JRW	
DATE: 09/11/75	
APPROVED BY: JCW	
DATE: 09/11/75	
REFERENCE: W-T8343-6	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION: EXTERNAL WIRING DIAGRAM
TYPE "T" W/O PROTECTOR

MATERIAL	PROCESS/FINISH
DECAL - 004169	

SIZE	DRAWING NUMBER	SHEET
A	4 of 6 005102-01	1 OF 1

Uncontrolled Copy

Data Sheet

Date: 29-06-2017
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

213TTDWD16347

Submittal


Data @ 200 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	12.2	12.7	15.4	18.6	23.0	24.8	27.8	140	
Torque (ft-lb)	0.00	5.5	11.0	16.6	22.3	25.5	28.0	45.3	
RPM	1800	1792	1784	1775	1765	1,755	1748	0	
Efficiency (%)		85.4	89.9	91.0	91.0	90.8	89.9		
P.F. (%)	5.2	37.4	58.1	71.3	77.1	81.4	80.6	44.8	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	700	1575	1765	1800
Current (Amps)	140	127	85.1	23.0	12.2
Torque (ft-lb)	45.3	40.0	66.1	22.3	0.00



Information Block

HP	7.5
Sync. RPM	1800
Frame	213
Enclosure	DP
Construction	TDW
Voltage	200 V
Frequency	60 Hz
Design	B
LR Code letter	H
Service Factor	1.15
Temp Rise @ FL	35 ° C
Duty	CONT
Ambient	40 ° C
Elevation	1,000 feet
Rotor/Shaft wk²	0.85 Lb-Ft²
Ref Wdg	K2134278 NONE
Sound Pressure @ 1M	66 dBA
VFD Rating	NONE
Outline Dwg	SS86596
Conn. Diag	005102.01

Additional Specifications:


0

365THFS8036

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.1440	0.1060	0.4930	0.6990	10.8610

Speed -Torque Curve



Uncontrolled Copy

CERTIFICATION DATA SHEET

Model#:	213TTDWD16347 AA	**WINDING#:**	K2134278 NONE 6
CONN. DIAGRAM:	005102.01	**ASSEMBLY:**	F1/F2 CAPABLE
OUTLINE:	SS86596-1115		

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
7 1/2	5.60	1800	1765	213JMV	DP	H	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60	200	23	ACROSS THE LINE	CONTINUOUS	F4	1.15	40	3300

FULL LOAD EFF: 91	3/4 LOAD EFF: 91	1/2 LOAD EFF: 89.9	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 77.1	3/4 LOAD PF: 71.3	1/2 LOAD PF: 58.1	89.5	SQ CAGE IND RUN	12.2

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
22.3 LB-FT	140.3	45.3 LB-FT 203	66.1 LB-FT 296	35

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
66 dBA	76 dBA	0.85 LB-FT^2	50 LB-FT^2	20 SEC.	2	125 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	ROUND	SHAFT DOWN	FALSE	NONE	TRUE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL 6309	BALL 6206	POLYREX EM	JM	NONE	NONE	AISI 1045 (C-240)	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

*
NOTES
*

DATE: 06/22/2017 05:08:27 AM
FORM 3531 REV.3 02/07/99
** Subject to change without notice.