marathon®

Washdown Motors

Model No: 213TTWWD16028
Catalog No: 141266.00M

Washdown Motor, 7.50 & 5 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 213TC Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 213TTWWD16028, Catalog No: 141266.00M Washdown Motor, 7.50 & 5 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 213TC Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**7.50 & 5 Hp**
Output KW	**5.6 & 3.7 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1765 & 1475 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**213TC**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91.7 & 90.2 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**19.6/9.8 & 16.6/8.3 A**
Power Factor	**78.3**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**H**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**


Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**1.18 O**	Mounting	**Round**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**T**	Overall Length	**18.77 in**
Frame Length	**9.65 in**	Shaft Diameter	**1 3/8 in**
Shaft Extension	**3.37 in**	Assembly/Box Mounting	**F1 Only**
Inverter Load	**Constant 10:1**		

Drawings

Connection Drawing	**005010.01ME**	Outline Drawing	**038045-965**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026





NOTES:
1- NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.
DASH 965 TO BE READ FROM OPPOSITE SHAFT END
2- C'BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING
BRACKETS AND TURNING FRAME 180 DEGREES (EXCEPT AS NOTED).

DASH	FRAME	C	BV	AG	MOUNTING
965	213T	18.77	10.755	15.65	
1115	213/15T	20.27	12.255	17.15	
1240	215T	21.52	13.505	18.40	F1 ONLY

DRAWING REVISION	REVISION BY	REV DATE/© DATE
D	SB	05/18/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026308	RMS	05/18/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±0.5°
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP
EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 125 INCH / 3.2 mm
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY	SL
DATE	10/09/15
APPROVED BY	GR
DATE	10/09/15
REFERENCE	
MATERIAL	
PROCESS/FINISH	
THIRD ANGLE PROJECTION	
SIZE	B
DRAWING NUMBER	038045
SHEET	1 OF 1

ORACLE REV
000

marathon™

DESCRIPTION
OUTLINE
WASHDOWN 210FR-TEFC-C-FACE-3PH

Uncontrolled Copy

Data Sheet

Date: 12/5/2018
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

213TTWWD16028

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	4.9	5.3	6.4	7.9	9.8	11.4	11.8	67.5	
Torque (ft-lb)	0.00	5.5	11.0	16.6	22.3	25.5	28.0	52.9	
RPM	1800	1792	1785	1775	1765	1,765	1762	0	
Efficiency (%)		86.4	90.6	91.6	91.7	91.1	90.8		
P.F. (%)	4.9	38.4	60.4	72.6	78.3	77.3	82.1	42.6	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1600	1765	1800
Current (Amps)	67.5	57.0	41.0	9.8	4.9
Torque (ft-lb)	52.9	49.0	75.0	22.3	0.00



Information Block

HP	7.5
Sync. RPM	1800
Frame	213
Enclosure	TEFC
Construction	TFR
Voltage	230/460#190/380 V
Frequency	60 Hz
Design	B
LR Code letter	H
Service Factor	1.15
Temp Rise @ FL	55 ° C
Duty	CONT
Ambient	40 ° C
Elevation	1,000 feet
Rotor/Shaft wk²	0.85 Lb-Ft²
Ref Wdg	K2134279 R1
Sound Pressure @ 1M	62 dBA
VFD Rating	NONE
Outline Dwg	038049-965
Conn. Diag	005010.01ME
Additional Specifications:	
0	
0	

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.7600	1.1080	2.4580	3.1730	50.4140

Speed -Torque Curve

