

Close-Coupled Pump Motors

Model No: 215TTFBD6012

Catalog No: GT3418A

Close-Coupled Pump Motor, 10 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 3600 RPM, 215JP
Frame, TEFC

Product Information Packet: Model No: 215TTFBD6012, Catalog No: GT3418A Close-Coupled Pump Motor, 10 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 3600 RPM, 215JP Frame, TEFC

Nameplate Specifications

Phase	3	Output HP	10 & 7.50 Hp
Output KW	7.5 & 5.6 kW	Voltage	230/460 & 190/380 V
Speed	3518 & 2925 r/min	Synchronous RPM	3600 & 3000 r/min
Service Factor	1.15 & 1.15	Frame	215JP
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	90.2 & 89.5 %	Ambient Temperature	40 °C
Frequency	60 & 50 Hz	Current	23.6/11.8 & 21.6/10.8 A
Power Factor	88	Duty	Continuous
Insulation Class	F	Design Code	B
KVA Code	H	Drive End Bearing Size	6309
Opp Drive End Bearing Size	6206	UL	Listed
CSA	Y	CE	Y
IP Code	43	Number of Speeds	1
Hazardous Location	DIVISION 2 T2B		



Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Reversible
Resistance Main	1.218 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JP	Overall Length	25.78 in
Frame Length	11.15 in	Shaft Diameter	1.25 in
Shaft Extension	8.39 in	Assembly/Box Mounting	F1/F2 Capable
Inverter Load	Constant 2:1/Variable 10:1		

Drawings

Connection Drawing	EE7308	Outline Drawing	SS620827-200
--------------------	--------	-----------------	--------------

4				3						2				1	
DASH NO.	B	C	D	E	2E	2F	2FF	AG	AH	BV	EQ	ET	MOUNTING	FRAME	
100	8.00	24.13	5.25	4.25	8.50	5.50	7.00	16.00	8.13	9.95	2.37	5.87	F1 OR F2	213JP	
200		25.63						17.50		11.45				215JP	




DRAWING REVISION G	REVISION BY SV	REV DATE/© DATE 06/01/2026
REQUEST NUMBER CR-0026504	APPROVED BY RMS	DATE 06/01/2026
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED		
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY



DRAWN BY ZHY		marathon™		
DATE 13-04-2017				
APPROVED BY		DESCRIPTION OUTLINE 213/215JP FR NEMA TEFC RS		
DATE				
REFERENCE		MATERIAL		PROCESS/FINISH
THIRD ANGLE PROJECTION		SIZE B		DRAWING NUMBER SS620827
				SHEET 1 OF 1

THREE PHASE
DUAL VOLTAGE MOTOR

HIGH VOLTAGE



LOW VOLTAGE



REF.
WINDING DIAGRAM

T8Y, T2Y, T2BL, T4BX, T2EC, T2G
T6BZ, T2B, T6BL, T4AV, T6B, T4B

OPTIONAL CORD
CONNECTION

L1 ——— WHITE ———
L2 ——— RED ———
L3 ——— BLACK ———

DRAWING REVISION J	REVISION BY SB	REV DATE/ © DATE 08/01/2025
REQUEST NUMBER CR-0023654	APPROVED BY SBD	DATE 08/01/2025
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED		
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		


PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY RM
DATE 11/20/1990
APPROVED BY SAS
DATE 04/24/2003
REFERENCE
THIRD ANGLE PROJECTION

marathon™		
DESCRIPTION CONN DIAGRAM-EXTERNAL 3Ø - DUAL VOLTAGE MOTOR		
MATERIAL		PROCESS/FINISH
SIZE A	DRAWING NUMBER EE7308	SHEET 1 OF 1

MARATHON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Customer**Curve at**460**Volts****HP** 10&7.5**PHASE** 3**Model No** 215TTFBD601260**HZ****VOLTS** 230/460&190/38010**HP****Catalog No** GT3418A**HZ** 60&50**RPM** 3518&2925**FL TORQUE** 14.9 Lb.Ft**BD TORQUE** 41.0 Lb.Ft**LR TORQUE** 28 Lb.Ft**FL AMPS** 23.6/11.8**PU TORQUE** 24.0 Lb.Ft**LR AMPS** 79**WINDING**

HE31322010-2

Prepared By

FAREEDA

Date

5/9/2018