marathon®

General Purpose Motors

Model No: 215TTFBD6027
Catalog No: GT1519

General Purpose Motor, 10 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 215T Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 215TTFBD6027, Catalog No: GT1519 General Purpose Motor, 10 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 215T Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**10 & 7.50 Hp**
Output KW	**7.5 & 5.6 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1762 & 1465 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**215T**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91.7 & 91 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**25/12.5 & 23.8/11.9 A**
Power Factor	**81.3**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**H**	Drive End Bearing Size	**6307**
Opp Drive End Bearing Size	**6206**	UL	**Listed**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**
Hazardous Location	**DIVISION 2 T2B**		

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**1.155 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**T**	Shaft Diameter	**1.375 in**
Assembly/Box Mounting	**F1/F2 Capable**	Inverter Load	**Constant 10:1/Variable 10:1**


Drawings


Connection Drawing	**EE7308**	Outline Drawing	**SS620737-200**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME
100	8.00	18.34	5.25	4.25	8.50	5.50	7.00	3.50	5.44	F1 OR F2	213T
200		19.84							6.94		215T







DRAWING REVISION: E	REVISION BY: SV	REV DATE/© DATE: 06/01/2026
REQUEST NUMBER: CR-0026504	APPROVED BY: RMS	DATE: 06/01/2026
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: WY	marathon™		
DATE: 25-02-2016			
APPROVED BY: ZYH	DESCRIPTION: OUTLINE 213/215T FR NEMA TEFC RS		
DATE: 25-02-2016			
REFERENCE	MATERIAL	PROCESS/FINISH	
THIRD ANGLE PROJECTION	SIZE: B	DRAWING NUMBER: SS620737	SHEET: 1 OF 1


Uncontrolled Copy


THREE PHASE
DUAL VOLTAGE MOTOR

HIGH VOLTAGE



LOW VOLTAGE





VIEW OF TERMINAL END

REF.
WINDING DIAGRAM

T8Y, T2Y, T2BL, T4BX, T2EC, T2G
T6BZ, T2B, T6BL, T4AV, T6B, T4B

OPTIONAL CORD CONNECTION

L1	WHITE
L2	RED
L3	BLACK

DRAWING REVISION: J	REVISION BY: SB	REV DATE/ © DATE: 08/01/2025
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: RM	
DATE: 11/20/1990	
APPROVED BY: SAS	
DATE: 04/24/2003	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
CONN DIAGRAM-EXTERNAL
3Ø - DUAL VOLTAGE MOTOR

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	4 of 5 EE7308	1 OF 1

Data Sheet

Date: 3/11/2024
Customer:
Attention:
Submitted by: RAMYA

marathon® Motors

215TTFBD6027

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	5.6	6.2	7.8	10.0	12.5	14.3	15.5	80.0	
Torque (ft-lb)	0.00	7.3	14.7	22.2	29.8	34.4	37.4	65.0	
RPM	1800	1792	1782	1772	1762	1,756	1752	0	
Efficiency (%)		88.5	90.8	91.8	91.7	90.3	89.5		
P.F. (%)	9.0	42.5	66.0	76.6	81.3	83.4	84.2	45.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1615	1762	1800
Current (Amps)	80.0	73.0	46.0	12.5	5.6
Torque (ft-lb)	65.0	50.0	85.0	29.8	0.00



Information Block

HP	10.0
Sync. RPM	1800
Frame	215
Enclosure	TEFC
Construction	TFB
Voltage	208-230/460#190/380 V
Frequency	60 Hz
Design	B
LR Code letter	H
Service Factor	1.15
Temp Rise @ FL	85 ° C
Duty	CONT
Ambient	40 ° C
Elevation	3,300 feet
Rotor/Shaft wk²	1.13 Lb-Ft²
Ref Wdg	HA31324013 NONE
Sound Pressure @ 1M	62 dBA
VFD Rating	CONSTANT 10:1/VARIABLE 10:1
Outline Dwg	SS620737-200
Conn. Diag	EE7308
Additional Specifications:	
0	
0	

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.7410	0.4660	2.1470	2.5790	46.7750

Speed -Torque Curve

