marathon®

Vertical Pump Motors

Model No: 215TTFWD16057
Catalog No: M885B

Vertical Pump Motor, 10 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 215HPV Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 215TTFWD16057, Catalog No: M885B Vertical Pump Motor, 10 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 215HPV Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**10 Hp**
Output KW	**7.5 kW**	Voltage	**230/460 V**
Speed	**1760 r/min**	Synchronous RPM	**1800 r/min**
Service Factor	**1.15**	Frame	**215HPV**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91.7 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**26.4/13.2 A**
Power Factor	**77.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**H**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.9 O**	Mounting	**Round**
Motor Orientation	**Shaft Down**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**HP**	Shaft Diameter	**1.125 in**
Assembly/Box Mounting	**F1/F2 Capable**		

Drawings

Connection Drawing	**EE7308**	Outline Drawing	**SS86643-1240**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 15/10/2026

SS86643



DASH	FR.	C	AG	BV
965	213T	21.16	18.41	10.66
1115	213/15T	22.66	19.91	12.16
1240	213/15T	23.91	21.16	13.41

NOTES:
1. NAMEPLATE TO BE READ FROM SHAFT EXT. END OF MOTOR.
2. BOX CAN BE MOUNTED IN 90° STEPS.

NO.	REVISION	BY & DATE	CHK
7	UPDATED DRAWING	TJW 04/30/2007	
6	REDRAWN IN AUTOCAD	TAT 07-22-2004	ML
5	ADDED ø9.12 B.C. & ø.437 (4) HOLES CN 29200-1501	HLB 02-27-2001	
4	UPDATED C' BOX GEOMETRY CN 28425	DRS 01-31-2000	
3	REMOVED GROUND SCREW FROM FRAME CN 24453	MJD 10-01-1997	

TOLERANCES UNLESS SPECIFIED	
DEC.	INCHES
.X	±.1
.XX	±.03
.XXX	±.005
.XXXX	±.0005
ANG	±7'30"

MARATHON ELECTRIC

DRAWN MRB 11-05-1996
CHK ML 11-07-1996
APPD DN 11-08-1996
SCALE 7=32
REF
FMF
PREV

TITLE OUTLINE
210T FR.-TEFC-P' BASE-R/S FRAME

MAT'L.
FINISH
CAD FILE ss86643

RFP
DIST LB

SIZE	DRAWING NO.	PAGE	OF	REV.
A	SS86643			7

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED
THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT

7/26/2007 3:03:16 PM -