marathon®

Washdown Motors

Model No: 215TTWD16026
Catalog No: 141276.00M

Washdown Motor, 10 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 215JM Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 215TTWD16026, Catalog No: 141276.00M Washdown Motor, 10 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 215JM Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**10 & 7.50 Hp**
Output KW	**7.5 & 5.6 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1760 & 1475 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**215JM**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91.7 & 89.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**26.4/13.2 & 27.4/13.7 A**
Power Factor	**77.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**H**	Drive End Bearing Size	**6209**
Opp Drive End Bearing Size	**6207**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**56**	Number of Speeds	**1**


Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.9 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Stainless Steel**
Shaft Type	**JM**	Overall Length	**19.81 in**
Frame Length	**12.0 in**	Shaft Diameter	**7/8 in**
Shaft Extension	**4.25 in**	Assembly/Box Mounting	**F1 Only**
Inverter Load	**Constant 3:1**		

Drawings

Connection Drawing	**005010.01ME**	Outline Drawing	**037618ME.00**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026





ISOMETRIC VIEW
SCALE 1=6

NO	REVISION	BY & DATE	CHK

TOLERANCES UNLESS SPECIFIED
DEC INCHES
.X ±.1
.XX ±.03
.XXX ±.005
.XXXX ±.0005
ANG ±1/2°

marathon electric

TITLE OUTLINE - 210TC FRAME
TEFC - RIGID "C" - JM PUMP
MAT'L WASHGUARD ALL STAINLESS STEEL MOTOR
FINISH
CAD FILE

DRAWN	PVR 10/24/13
CHK	JD 10/24/13
APPR	
SCALE	3:8
REF	037618
FMF	213TTWD14002
PREV	

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED.
THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT

RFP
DIST 037618ME

SIZE B
DRAWING NO 037618ME
REV

Data Sheet

Date: 6/29/2017
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

215TTWD16026

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	7.2	7.7	9.0	11.0	13.2	14.8	15.9	81.0	
Torque (ft-lb)	0.00	7.3	14.8	22.3	29.9	34.5	37.6	76.0	
RPM	1800	1790	1780	1770	1760	1,754	1747	0	
Efficiency (%)		86.4	91.0	91.7	91.7	90.9	90.5		
P.F. (%)	4.8	35.4	57.2	69.6	77.5	80.1	81.3	42.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1575	1760	1800
Current (Amps)	81.0	78.0	51.0	13.2	7.2
Torque (ft-lb)	76.0	70.0	90.0	29.9	0.00




Information Block

HP	10.0
Sync. RPM	1800
Frame	215
Enclosure	TEFC
Construction	TFW
Voltage	230/460#190/380 V
Frequency	60 Hz
Design	B
LR Code letter	H
Service Factor	1.15
Temp Rise @ FL	65 ° C
Duty	CONT
Ambient	40 ° C
Elevation	1,000 feet
Rotor/Shaft wk²	1.10 Lb-Ft²
Ref Wdg	K2154513 NONE
Sound Pressure @ 1M	62 dBA
VFD Rating	CONSTANT 3:1
Outline Dwg	037618-1200
Conn. Diag	005010.01ME
Additional Specifications:	
0	
0	

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.5840	0.5050	1.7640	2.1360	36.0320

Speed -Torque Curve



Uncontrolled Copy

CERTIFICATION DATA SHEET

Model#:	215TTWD16026 AA	**WINDING#:**	K2154513 NONE 3
CONN. DIAGRAM:	005010.01ME	**ASSEMBLY:**	F1 ONLY
OUTLINE:	037618-1200		

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
10&7 1/2	7.50&5.60	1800	1760&1465	215JM	TEFC	H	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	230/460#190/380	26.4/13.2&24.6/12.3	LINE OR INVERTER	CONTINUOUS	F4	1.15/1.15	40	3300

FULL LOAD EFF: 91.7&90.7	3/4 LOAD EFF: 91.7	1/2 LOAD EFF: 91	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 77.5&76	3/4 LOAD PF: 69.6	1/2 LOAD PF: 57.2	90.2	SQ CAGE INV RATED	14.3 / 7.2

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
29.9 LB-FT	162 / 81	76 LB-FT 255	90 LB-FT 302	65

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
62 dBA	72 dBA	1.1 LB-FT^2	50 LB-FT^2	20 SEC.	2	150 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	NO PAINT

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL 6209	BALL 6207	POLYREX EM	JM	NONE	NONE	303 STAINLESS (C-501)	STAINLESS STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

INVERTER TORQUE: CONSTANT 3:1
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

*
NOTES
*

DATE: 06/23/2017 01:02:27 AM
FORM 3531 REV.3 02/07/99
** Subject to change without notice.