marathon®

Close-Coupled Pump Motors

Model No: 254TTDBD6046
Catalog No: GT4459

Close-Coupled Pump Motor, 15 & 10 HP, 3 Ph, 60 & 50 Hz, 208-230/460 & 190/380 V, 1800 RPM, 254JPV Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 254TTDBD6046, Catalog No: GT4459 Close-Coupled Pump Motor, 15 & 10 HP, 3 Ph, 60 & 50 Hz, 208-230/460 & 190/380 V, 1800 RPM, 254JPV Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**15 & 10 Hp**
Output KW	**11.2 & 7.5 kW**	Voltage	**208-230/460 & 190/380 V**
Speed	**1774 & 1478 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**254JPV**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**93 & 92.3 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**40.5-37.5/18.8 & 32/16 A**
Power Factor	**81**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6208**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications

Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.6729 O**	Mounting	**Round**
Motor Orientation	**Shaft Down**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**JP**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 2:1/Variable 10:1**		

Drawings

Connection Drawing	**EE7308K**	Outline Drawing	**SS621216-100**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026