marathon®

Close-Coupled Pump Motors

Model No: 256TTFCD6012
Catalog No: GT3424A

Close-Coupled Pump Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 3600 RPM, 256JP Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 256TTFCD6012, Catalog No: GT3424A Close-Coupled Pump Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 3600 RPM, 256JP Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**20 & 15 Hp**
Output KW	**14.9 & 11.2 kW**	Voltage	**230/460 & 190/380 V**
Speed	**3540 & 2945 r/min**	Synchronous RPM	**3600 & 3000 r/min**
Service Factor	**1.15 & 1.15**	Frame	**256JP**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91 & 90.2 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**47/23.5 & 43.5/21.7 A**
Power Factor	**88**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6209**	UL	**Listed**
CSA	**Y**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**
Hazardous Location	**DIVISION 2 T2B**		

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**2**	Rotation	**Reversible**
Resistance Main	**.561 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**JP**	Overall Length	**30.76 in**
Frame Length	**11.73 in**	Shaft Diameter	**1.375 in**
Shaft Extension	**8.37 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 2:1/Variable 10:1**		


Drawings


Connection Drawing	**EE7308K**	Outline Drawing	**SS620809-200**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	E	2E	2F	2FF	AG	AH	BV	EQ	ET	MOUNTING	FRAME
100	9.60	29.03	5.00	10.00	---	8.50	20.91	8.121	9.14	2.37	5.87	F1 OR F2	254JP
200	11.34	30.76			8.50	10.00	22.64		10.00				254/256JP







DRAWING REVISION D	REVISION BY SB	REV DATE/© DATE 05/28/2026
REQUEST NUMBER CR-0026424	APPROVED BY RMS	DATE 05/28/2026
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		


COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY


DRAWN BY SN		marathon™
DATE 12/04/2017		
APPROVED BY SBD		DESCRIPTION: OUTLINE 254/256 JP FR NEMA TEFC-CAST IRON
DATE 12/04/2017		
REFERENCE	MATERIAL	PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE B / DRAWING NUMBER SS620809	SHEET 1 OF 1


Uncontrolled Copy

LOW VOLTAGE



HIGH VOLTAGE





VIEW OF TERMINAL END

DRAWING REVISION: F	REVISION BY: SB	REV DATE/ © DATE: 08/01/2025	DRAWN BY: PGK	marathon™
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025	DATE: 06/04/1997	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED			APPROVED BY: GK	DESCRIPTION: CONN DIAGRAM-EXTERNAL DELTA CON. - 3ø - 9 LEADS
			DATE: 06/15/1997	
			REFERENCE	MATERIAL / PROCESS/FINISH
			THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: EE7308K / SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED.
PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

Uncontrolled Copy


MARATHON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Customer

Curve at 460 **Volts** **HP** 20&15 **PHASE** 3
60 **HZ**
Model No 256TTFCD6012 20 **HP** **VOLTS** 230/460&190/380

Catalog No GT3424A **HZ** 60&50 **RPM** 3540&2945



Torque in Lb.Ft

FL TORQUE	29.7	**Lb.Ft**	**FL AMPS**	47.5/23.7	
BD TORQUE	74.0	**Lb.Ft**	**PU TORQUE**	41.0	**Lb.Ft**
LR TORQUE	49	**Lb.Ft**	**LR AMPS**	143	
WINDING	HE31602007-2	**Prepared By**	FAREEDA	**Date**	5/4/2018