marathon®

Close-Coupled Pump Motors

Model No: 284TTFCD6082
Catalog No: GT3123A

Close-Coupled Pump Motor, 15 & 10 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1200 RPM, 284JM Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 284TTFCD6082, Catalog No: GT3123A Close-Coupled Pump Motor, 15 & 10 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1200 RPM, 284JM Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**15 & 10 Hp**
Output KW	**11.2 & 7.5 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1182 & 985 r/min**	Synchronous RPM	**1200 & 1000 r/min**
Service Factor	**1.15 & 1.15**	Frame	**284JM**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91.7 & 91 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**40/20 & 34.5/17.2 A**
Power Factor	**77.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6311**
Opp Drive End Bearing Size	**6211**	UL	**Listed**
CSA	**Y**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**
Hazardous Location	**DIVISION 2 T2B**		

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Part Wdg Start Low Volt Only & Wye Start Delta Run Or Inverter**
Poles	**6**	Rotation	**Reversible**
Resistance Main	**.7445 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**JM**	Overall Length	**27.52 in**
Frame Length	**11.41 in**	Shaft Diameter	**1.375 in**
Shaft Extension	**5.5 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 10:1/Variable 10:1**		


Drawings


Connection Drawing	**EE7308AA**	Outline Drawing	**SS620797-100**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	E	2E	2F	2FF	AG	AH	BA	BV	EQ	ET	MOUNTING	FRAME
100	10.83	27.52	5.50	11.00	---	9.50	22.27	5.25	4.75	9.76	0.62	2.99	F1 OR F2	284JM
200	12.68	29.02			9.50	11.00	23.77			10.50				284/286JM








DRAWING REVISION: E	REVISION BY: CP	REV DATE/© DATE: 05/26/2026
REQUEST NUMBER: CR-0026396	APPROVED BY: RMS	DATE: 05/26/2026
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		


COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY


DRAWN BY: SN	marathon™
DATE: 12/04/2017	
APPROVED BY: SBD	DESCRIPTION: OUTLINE 284/286 JM FR NEMA TEFC-CAST IRON
DATE: 12/04/2017	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: B / DRAWING NUMBER: SS620797 / SHEET: 1 OF 1



LOW VOLTAGE



HIGH VOLTAGE



VIEW OF TERMINAL END

DRAWING REVISION: L	REVISION BY: SB	REV DATE/© DATE: 08/01/2025	PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY: LZ	marathon™
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025		DATE: 01-12-1994	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED				APPROVED BY: GK	DESCRIPTION: CONN DIAGRAM-EXTERNAL 3Ø-2/1 DELTA-12 LEADS
				DATE: 01-14-1994	
				REFERENCE	MATERIAL / PROCESS/FINISH
				THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: EE7308AA / SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

Uncontrolled Copy

MARATHON ELECTRIC CORPORATION


TYPICAL PERFORMANCE CURVE for AC MOTOR

Customer

Curve at 460 **Volts** **HP** 15&10 **PHASE** 3
60 **HZ**
15 **HP** **VOLTS** 230/460&190/380

Model No 284TTFCD6082

Catalog No GT3123A **HZ** 60&50 **RPM** 1182&985



Torque in Lb.Ft

FL TORQUE	66.7 **Lb.Ft**		**FL AMPS**	40/20	
BD TORQUE	157.0 **Lb.Ft**		**PU TORQUE**	97.0	**Lb.Ft**
LR TORQUE	115 **Lb.Ft**		**LR AMPS**	116	
WINDING	HE31806006-2	**Prepared By** FAREEDA		**Date**	5/4/2018