marathon®

Vertical Pump Motors

Model No: 284TTFNA16015
Catalog No: M896B

Vertical Pump Motor, 25 HP, 3 Ph, 60 Hz, 230/460 V, 3600 RPM, 284HPV Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 284TTFNA16015, Catalog No: M896B Vertical Pump Motor, 25 HP, 3 Ph, 60 Hz, 230/460 V, 3600 RPM, 284HPV Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**25 Hp**
Output KW	**18.7 kW**	Voltage	**230/460 V**
Speed	**3555 r/min**	Synchronous RPM	**3600 r/min**
Service Factor	**1.15**	Frame	**284HPV**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**93.6 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**56.0/28.1 A**
Power Factor	**89**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6311**
Opp Drive End Bearing Size	**6210**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**


Technical Specifications

Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**2**	Rotation	**Reversible**
Resistance Main	**.356 O**	Mounting	**Round**
Motor Orientation	**Shaft Down**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**HP**	Overall Length	**30.84 in**
Frame Length	**14.25 in**	Shaft Diameter	**1 1/8 in**
Shaft Extension	**2.75 in**	Assembly/Box Mounting	**F1/F2 Capable**

Drawings

Connection Drawing	**EE7308**	Outline Drawing	**B-SS311022-1425**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026



NOTES:
1. BOX CAN ONLY BE ROTATED CLOCKWISE UP TO 270° FROM ITS ORIGINAL POSITION.
2. NAMEPLATE TO BE READ FROM CONDUIT BOX SIDE OF MOTOR.

DASH	FRAME		AG	C			BV
1425	284/286HP		28.09	30.84			12.13
1475	284/286HP		28.59	31.34			12.38

NO.	REVISION	BY & DATE	CHK
3	REDRAW ON AUTOCAD	HLB 09-07-2004	ML
2	CORRECTED C'BOX HOLE NOTE CN 29200-1454	HLB 02-16-2001	
1	NEW DRAWING MU25722	DRS 04-06-2000	

TOLERANCES UNLESS SPECIFIED: DEC. INCHES; .X ±.1; .XX ±.03; .XXX ±.005; .XXXX ±.0005; ANG ±7'30"

MARATHON ELECTRIC

TITLE OUTLINE - TEFC - TGN
280HP FR. - BB - STD - 12.50 LAM

MAT'L.

FINISH

CAD FILE ss311022

RFP

DIST LB

DRAWN DRS 03-30-2000
CHK ML 04-06-2000
APPD GK 04-06-2000
SCALE 1=5
REF
FMF
PREV


SIZE	DRAWING NO.	PAGE OF	REV.
B	SS311022		3

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED
THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT


Uncontrolled Copy


THREE PHASE
DUAL VOLTAGE MOTOR

HIGH VOLTAGE



LOW VOLTAGE





VIEW OF TERMINAL END

REF.
WINDING DIAGRAM

T8Y, T2Y, T2BL, T4BX, T2EC, T2G
T6BZ, T2B, T6BL, T4AV, T6B, T4B

OPTIONAL CORD CONNECTION

L1	WHITE
L2	RED
L3	BLACK

DRAWING REVISION: J	REVISION BY: SB	REV DATE/ © DATE: 08/01/2025
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: RM	
DATE: 11/20/1990	
APPROVED BY: SAS	
DATE: 04/24/2003	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
CONN DIAGRAM-EXTERNAL
3Ø - DUAL VOLTAGE MOTOR

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	4 of 5 EE7308	1 OF 1

Uncontrolled Copy

Data Sheet

Date: 11/30/2018
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

284TTFNA16015

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	8.0	10.5	15.5	21.5	28.1	31.0	35.0	180	
Torque (ft-lb)	0.00	9.0	18.5	27.5	37.0	42.0	46.5	55.0	
RPM	3600	3590	3580	3565	3555	3,550	3540	0	
Efficiency (%)		89.5	93.0	93.6	93.6	93.0	92.4		
P.F. (%)	14.5	63.5	81.5	87.5	89.0	89.0	90.0	34.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	1800	3350	3555	3600
Current (Amps)	180	165	110	28.1	8.0
Torque (ft-lb)	55.0	55.0	104	37.0	0.00



Information Block

HP	25.0	
Sync. RPM	3600	
Frame	284	
Enclosure	TEFC	
Construction	TFS	
Voltage	230/460	V
Frequency	60	Hz
Design	A	
LR Code letter	G	
Service Factor	1.15	
Temp Rise @ FL	50	° C
Duty	CONT	
Ambient	40	° C
Elevation	1,000	feet
Rotor/Shaft wk²	2.70	Lb-Ft²
Ref Wdg	K284261 NONE	
Sound Pressure @ 1M	72	dBA
VFD Rating	NONE	
Outline Dwg	B-SS311022-1425	
Conn. Diag	A-EE7308	
Additional Specifications:		
0		
0		

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.2050	0.1210	0.9230	0.6840	33.6740

Speed -Torque Curve

