marathon®

Close-Coupled Pump Motors

Model No: 286TTDBD6082
Catalog No: GT0463

Close-Coupled Pump Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1200 RPM, 286JM Frame, DP

©2026 Marathon, All Rights Reserved.


marathon®


Product Information Packet: Model No: 286TTDBD6082, Catalog No: GT0463 Close-Coupled Pump Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1200 RPM, 286JM Frame, DP


Nameplate Specifications			
Phase	**3**	Output HP	**20 & 15 Hp**
Output KW	**14.9 & 11.2 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1182 & 985 r/min**	Synchronous RPM	**1200 & 1000 r/min**
Service Factor	**1.15 & 1.15**	Frame	**286JM**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**92.4 & 91.7 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**52.5/26.3 & 48.5/24.3 A**
Power Factor	**77**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**F**	Drive End Bearing Size	**6311**
Opp Drive End Bearing Size	**6210**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**
Technical Specifications			
Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Part Wdg Start Low Volt Only & Wye Start Delta Run Or Inverter**
Poles	**6**	Rotation	**Reversible**
Resistance Main	**.5345 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**JM**	Overall Length	**27.09 in**
Frame Length	**13.97 in**	Shaft Diameter	**1.249 in**
Shaft Extension	**5.25 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Variable 10:1**		
Drawings			
Connection Drawing	**EE7308AA**	Outline Drawing	**SS620823-200**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	AG	AH	BV	EQ	ET	MOUNTING	FRAME
100	15.55	26.48	7.00	5.50	11.00	9.50	11.00	21.24	5.248	15.80	0.63	3.00	F1 OR F2	284JM
200		27.86						22.61		17.18				286JM







DRAWING REVISION	REVISION BY	REV DATE/© DATE
E	MN	07/17/2025
REQUEST NUMBER	APPROVED BY	DATE
NMR-0238038	VS	07/17/2025

REQUEST NUMBER DESCRIPTION
F2 MOUNTING PLATE ADDED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	


REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200/ 5.1/ INCH mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	DESCRIPTION
VS	OUTLINE
DATE	284/286JM FR NEMA ODP RS
12/02/2021	
APPROVED BY	
GNK	
DATE	
12/02/2021	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE B / DRAWING NUMBER SS620823 / SHEET 1 OF 1


marathon™



LOW VOLTAGE



HIGH VOLTAGE



VIEW OF TERMINAL END

DRAWING REVISION: L	REVISION BY: SB	REV DATE/© DATE: 08/01/2025	PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY: LZ	marathon™
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025		DATE: 01-12-1994	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED				APPROVED BY: GK	DESCRIPTION: CONN DIAGRAM-EXTERNAL 3Ø-2/1 DELTA-12 LEADS
				DATE: 01-14-1994	
				REFERENCE	MATERIAL / PROCESS/FINISH
				THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: EE7308AA / SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

Data Sheet

Date: 12/1/2021
Customer:
Attention:
Submitted by:

marathon® Motors

286TTDBD6082

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	13.2	14.2	17.1	21.3	26.3	29.8	32.2	138	
Torque (ft-lb)	0.00	22.0	44.0	66.4	89.0	102	112	150	
RPM	1200	1195	1192	1188	1182	1,180	1178	0	
Efficiency (%)		87.5	91.7	92.4	92.4	91.7	91.0		
P.F. (%)	4.5	37.5	59.5	71.0	77.0	80.0	79.0	41.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	600	1105	1182	1200
Current (Amps)	138	122	85.0	26.3	13.2
Torque (ft-lb)	150	128	217	89.0	0.00



Information Block

HP	20.0	
Sync. RPM	1200	
Frame	286	
Enclosure	DP	
Construction	TDB	
Voltage	230/460#190/380	V
Frequency	60	Hz
Design	B	
LR Code letter	F	
Service Factor	1.15	
Temp Rise @ FL	50	° C
Duty	CONT	
Ambient	40	° C
Elevation	3,300	feet
Rotor/Shaft wk²	6.0	Lb-Ft²
Ref Wdg	HA31806007 NONE	
Sound Pressure @ 1M	65	dBA
VFD Rating	VARIABLE 20:1	
Outline Dwg	SS620823-200	
Conn. Diag	EE7308AA	

Additional Specifications:

0

0

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.3450	0.1670	0.9880	1.4610	20.3770

Speed -Torque Curve

