marathon®

Close-Coupled Pump Motors

Model No: 286TTDBD6095
Catalog No: GT2563

Close-Coupled Pump Motor, 20 HP, 3 Ph, 60 Hz, 575 V, 1200 RPM, 286JP Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 286TTDBD6095, Catalog No: GT2563 Close-Coupled Pump Motor, 20 HP, 3 Ph, 60 Hz, 575 V, 1200 RPM, 286JP Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**20 Hp**
Output KW	**14.9 kW**	Voltage	**575 V**
Speed	**1182 r/min**	Synchronous RPM	**1200 r/min**
Service Factor	**1.15**	Frame	**286JP**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**92.4 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**21.1 A**
Power Factor	**77**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**F**	Drive End Bearing Size	**6311**
Opp Drive End Bearing Size	**6210**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**6**	Rotation	**Reversible**
Resistance Main	**.5345 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**JP**	Overall Length	**30.91 in**
Frame Length	**13.97 in**	Shaft Diameter	**1.249 in**
Shaft Extension	**8.4 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Variable 10:1**		


Drawings

Connection Drawing	**EE7300**	Outline Drawing	**SS620826-200**


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 15/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	AG	AH	BV	EQ	ET	MOUNTING	FRAME
100	15.55	29.36	7.00	5.50	11.00	9.50	11.00	21.24	8.126	15.80	2.37	5.88	F1 OR F2	284JP
200		30.74						22.61		17.18				284/286JP





F2 VIEW



DRAWING REVISION	REVISION BY	REV DATE/© DATE
D	VS	23RD JULY 25
REQUEST NUMBER	APPROVED BY	DATE
NMR-0238040	VS	23RD JULY 25

REQUEST NUMBER DESCRIPTION
ADDED F2 MOUNTING PLATE

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 / INCH 5.1 / mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	WY
DATE	17/04/2017
APPROVED BY	ZYH
DATE	17/04/2017
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
OUTLINE
284/286JP FR NEMA ODP RS


MATERIAL | PROCESS/FINISH

SIZE B | DRAWING NUMBER SS620826 | SHEET 1 OF 1

THREE PHASE - SINGLE VOLTAGE
MOTOR - CONDUIT BOX @ 'A'


TO REVERSE ROTATION:
INTERCHANGE ANY TWO LINE
LEAD CONNECTIONS

TERMINAL BLOCK WHEN SPECIFIED




VIEW OF TERMINAL END

IF MOTOR HAS
9 LEADS



IF MOTOR HAS
6 LEADS



A-9806 DECAL

OPTIONAL CORD
CONNECTION

L1	WHITE
L2	RED
L3	BLACK

DRAWING REVISION: AD	REVISION BY: SB	REV DATE/© DATE: 08/01/2025
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: DA	
DATE: 03-26-1993	
APPROVED BY: TB	
DATE: 03-26-1993	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
CONNECTION DIAGRAM
EXTERNAL - SINGLE VOLTAGE - 3Ø MOTOR

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	EE7300	1 OF 1

Data Sheet

Date: 12/1/2021
Customer:
Attention:
Submitted by:

marathon® Motors

286TTDBD6095

Submittal


Data @ 575 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	10.6	11.4	13.7	17.0	21.0	23.8	25.8	110	
Torque (ft-lb)	0.00	22.0	44.0	66.4	89.0	102	112	150	
RPM	1200	1195	1192	1188	1182	1,180	1178	0	
Efficiency (%)		87.5	91.7	92.4	92.4	91.7	91.0		
P.F. (%)	4.5	37.5	59.5	71.0	77.0	80.0	79.0	41.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	600	1105	1182	1200
Current (Amps)	110	97.6	68.0	21.0	10.6
Torque (ft-lb)	150	128	217	89.0	0.00



Information Block

HP	20.0	
Sync. RPM	1200	
Frame	286	
Enclosure	DP	
Construction	TDB	
Voltage	575	V
Frequency	60	Hz
Design	B	
LR Code letter	F	
Service Factor	1.15	
Temp Rise @ FL	50	° C
Duty	CONT	
Ambient	40	° C
Elevation	3,300	feet
Rotor/Shaft wk²	6.0	Lb-Ft²
Ref Wdg	HA31806007 NONE	
Sound Pressure @ 1M	65	dBA
VFD Rating	VARIABLE 20:1	
Outline Dwg	SS620826-200	
Conn. Diag	EE7300	
Additional Specifications:		
0		
0		

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.5380	0.2610	1.5440	2.2820	31.8390

Speed -Torque Curve

