marathon®

Close-Coupled Pump Motors

Model No: 286TTDBD6033
Catalog No: GT0567

Close-Coupled Pump Motor, 30 HP, 3 Ph, 60 Hz, 575 V, 1800 RPM, 286JM Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 286TTDBD6033, Catalog No: GT0567 Close-Coupled Pump Motor, 30 HP, 3 Ph, 60 Hz, 575 V, 1800 RPM, 286JM Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**30 Hp**
Output KW	**22.4 kW**	Voltage	**575 V**
Speed	**1775 r/min**	Synchronous RPM	**1800 r/min**
Service Factor	**1.15**	Frame	**286JM**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**94.1 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**29.2 A**
Power Factor	**82**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6311**
Opp Drive End Bearing Size	**6210**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.289 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**JM**	Overall Length	**27.09 in**
Frame Length	**13.97 in**	Shaft Diameter	**1.249 in**
Shaft Extension	**5.25 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 2:1/Variable 10:1**		


Drawings


Connection Drawing	**EE7300**	Outline Drawing	**SS620823-200**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 15/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	AG	AH	BV	EQ	ET	MOUNTING	FRAME
100	15.55	26.48	7.00	5.50	11.00	9.50	11.00	21.24	5.248	15.80	0.63	3.00	F1 OR F2	284JM
200		27.86						22.61		17.18				286JM







DRAWING REVISION	REVISION BY	REV DATE/© DATE
E	MN	07/17/2025
REQUEST NUMBER	APPROVED BY	DATE
NMR-0238038	VS	07/17/2025

REQUEST NUMBER DESCRIPTION
F2 MOUNTING PLATE ADDED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200/ 5.1/ INCH mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY


DRAWN BY	DESCRIPTION
VS	OUTLINE
DATE	284/286JM FR NEMA ODP RS
12/02/2021	
APPROVED BY	
GNK	
DATE	
12/02/2021	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE B / DRAWING NUMBER SS620823 / SHEET 1 OF 1

marathon™

THREE PHASE - SINGLE VOLTAGE
MOTOR - CONDUIT BOX @ 'A'


TO REVERSE ROTATION:
INTERCHANGE ANY TWO LINE
LEAD CONNECTIONS

TERMINAL BLOCK WHEN SPECIFIED




VIEW OF TERMINAL END

IF MOTOR HAS
9 LEADS



IF MOTOR HAS
6 LEADS



A-9806 DECAL

OPTIONAL CORD
CONNECTION

L1	WHITE
L2	RED
L3	BLACK

DRAWING REVISION: AD	REVISION BY: SB	REV DATE/© DATE: 08/01/2025
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: DA	
DATE: 03-26-1993	
APPROVED BY: TB	
DATE: 03-26-1993	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
CONNECTION DIAGRAM
EXTERNAL - SINGLE VOLTAGE - 3Ø MOTOR

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	EE7300	1 OF 1

Data Sheet

Date: 12/1/2021
Customer:
Attention:
Submitted by:

marathon® Motors

286TTDBD6033

Submittal


Data @ 575 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	12.4	14.0	18.0	23.2	29.2	32.8	35.6	180	
Torque (ft-lb)	0.00	22.0	44.0	66.5	88.8	102	111	173	
RPM	1800	1795	1788	1780	1775	1,770	1765	0	
Efficiency (%)		90.2	93.6	94.1	94.1	94.1	93.6		
P.F. (%)	4.5	44.0	66.0	77.0	82.0	83.0	84.0	38.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1645	1775	1800
Current (Amps)	180	142	104	29.2	12.4
Torque (ft-lb)	173	150	235	88.8	0.00



Information Block

HP	30.0	
Sync. RPM	1800	
Frame	286	
Enclosure	DP	
Construction	TDB	
Voltage	575	V
Frequency	60	Hz
Design	B	
LR Code letter	G	
Service Factor	1.15	
Temp Rise @ FL	55	° C
Duty	CONT	
Ambient	40	° C
Elevation	3,300	feet
Rotor/Shaft wk²	4.8	Lb-Ft²
Ref Wdg	HA31804015 NONE	
Sound Pressure @ 1M	75	dBA
VFD Rating	VARIABLE 20:1	
Outline Dwg	SS620823-200	
Conn. Diag	EE7300	
Additional Specifications:		
0		
0		

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.2660	0.1770	1.0480	1.4030	28.0250

Speed -Torque Curve

