

Severe Duty Motors

Model No: 364THFCD9036

Catalog No: W587A

Severe Duty Motor, 60 HP, 3 Ph, 60 Hz, 460 V, 1800 RPM, 364T Frame, TEFC

Product Information Packet: Model No: 364THFCD9036, Catalog No: W587A Severe Duty Motor, 60 HP, 3 Ph, 60 Hz, 460 V, 1800 RPM, 364T Frame, TEFC

Nameplate Specifications

Phase	3	Output HP	60 Hp
Output KW	45.0 kW	Voltage	460 V
Speed	1780 r/min	Synchronous RPM	1800 r/min
Service Factor	1.15	Frame	364T
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	95 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	68.0 A
Power Factor	87.2	Duty	Continuous
Insulation Class	H	Design Code	B
KVA Code	G	Drive End Bearing Size	6313
Opp Drive End Bearing Size	6213	UL	Listed
CSA	Y	CE	Y
IP Code	56	Number of Speeds	1
Hazardous Location	DIVISION 2 T2B		




Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.104 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Shaft Diameter	2.375 in
Assembly/Box Mounting	F1/F2 Capable	Inverter Load	Constant 2:1/Variable 10:1

Drawings

Connection Drawing	EE7300U	Outline Drawing	SS557662-100
--------------------	----------------	-----------------	---------------------

4					3					2		1	
DASH NO.	B	C	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME			
100	14.96	33.40	7.00	14.00	-	11.25	5.88	6.12	F1 OR F2	364T			
200	15.94	34.40			11.25	12.25		6.62		364/365T			




DRAWING REVISION D	REVISION BY SB	REV DATE/© DATE 07/24/2025
REQUEST NUMBER CR-0023556	APPROVED BY SBD	DATE 07/24/2025
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED		
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		


PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY BISWA	marathon™		
DATE 01/10/2018			
APPROVED BY SBD	DESCRIPTION OUTLINE		
DATE 01/10/2018	364/365T FR-NEMA-SD & IEEE841		
REFERENCE	MATERIAL	PROCESS/FINISH	
THIRD ANGLE PROJECTION	SIZE B	DRAWING NUMBER SS557662	SHEET 1 OF 1

IF MOTOR HAS 9 LEADS





IF MOTOR HAS 6 LEADS



A-9806 DECAL IF CALLED FOR

IF MOTOR HAS 12 LEADS



VIEW OF TERMINAL END

DRAWING REVISION M	REVISION BY SB	REV DATE/© DATE 08/01/2025
REQUEST NUMBER CR-0023654	APPROVED BY SBD	DATE 08/01/2025
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED		
<small>COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.</small>		


PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY DRS
DATE 09-27-1996
APPROVED BY GK
DATE 09-30-1996
REFERENCE
THIRD ANGLE PROJECTION

marathon™

DESCRIPTION
CONN DIAGRAM-EXTERNAL
3Ø SINGLE VOLTAGE

MATERIAL		PROCESS/FINISH	
SIZE A	DRAWING NUMBER EE7300U		SHEET 1 OF 1





DATA VOLTS: 460

CERTIFICATION DATA SHEET

CONN. DIAGRAM: EE7300U
 OUTLINE: SS557662-364T
 WINDING: HE32254010 NONE 1

REFERENCE MODEL #: 364THFCD9036
 CAT #: W587A

MOUNTING: F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC RPM	FL RPM	FRAME	ENCLOSURE	TYPE	KVA CODE	DESIGN
60	45	1800	1782	364T	TEFC	TFC	G	B

PH	HZ	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB (° C)	ELEV.(Ft)
3	60	460	69	LINE OR INVERTER	CONT	H	1.15	40	3300

F.L. EFF	95.0	3/4 LD EFF	95.4	1/2 LD EFF	95.0	GTD EFF	ELECT. TYPE
F.L. PF	85.5	3/4 LD PF	83.0	1/2 LD PF	75.5	94.5	SQ CAGE INV RATED

F.L. TORQUE	LR AMPS @ 460 V	L.R. TORQUE	B.D. TORQUE	F.L. RISE (° C)
177 LB-FT	435	354 LB-FT 200%	451 LB-FT 255%	55

SOUND PRESSURE @	SOUND	ROTOR WK²	MAX. LOAD WK²	SAFE STALL TIME	STARTS/HOUR	APROX.
72 dBA	81 dBA	17.2 LB-FT²	425 LB-FT²	25 SEC.	2	398 LB.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	MOTOR ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	PREMIUM SEVERE DUTY	DIVISION 2 T2B	NO	NONE	BLUE (EPOXY)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT	MATERIAL	FRAME MATERIAL
DE	ODE							
BALL	BALL	POLYREX EM	T	NONE	NONE	1045 HOT ROLLED (C-204)		CAST IRON
6313	6213							

THERMOSTATS	PROTECTORS	WDG RTD's	BRG RTD's	THERMISTORS	CONTROL	SPACE	HEATERS
NONE	NOT	NONE	NONE	NONE	FALSE		NA

R1 (ohms/ph)	R2 (ohms/ph)	X1 (ohms/ph)	X2 (ohms/ph)	Xm (ohms/ph)	VIBRATION (in/sec)	FLOAT
0.064	0.04	0.364	0.487	11.723	0.080	ODE

* N O T E S *		<p>If Inverter equals NONE, contact factory for further information</p> <p>INVERTER TORQUE: VARIABLE 10:1</p> <p>INV. HP SPEED RANGE: NONE</p>
	<p>ENCODER: NONE</p> <p>NONE</p> <p>NONE</p> <p>NONE PPR</p>	
<p>PREPARED BY: ANUSHA M</p> <p>DATE: 3/18/2020</p>	<p>BRAKE: NONE</p> <p>NONE</p> <p>FT-LB: NA</p> <p>VOLTAGE: NONE</p> <p>NONE</p> <p>HZ:</p>	

FORM: 3531 REV_4 2/27/06
 ** Subject to change without notice.