marathon®

Vertical Pump Motors

Model No: 365TTFS16013
Catalog No: M916B

Vertical Pump Motor, 75 HP, 3 Ph, 60 Hz, 230/460 V, 3600 RPM, 365HPV Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 365TTFS16013, Catalog No: M916B Vertical Pump Motor, 75 HP, 3 Ph, 60 Hz, 230/460 V, 3600 RPM, 365HPV Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**75 Hp**
Output KW	**56.0 kW**	Voltage	**230/460 V**
Speed	**3555 r/min**	Synchronous RPM	**3600 r/min**
Service Factor	**1.15**	Frame	**365HPV**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**93.6 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**168.0/84.0 A**
Power Factor	**88.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6312**
Opp Drive End Bearing Size	**6312**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**


Technical Specifications

Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**2**	Rotation	**Reversible**
Resistance Main	**.07 O**	Mounting	**Round**
Motor Orientation	**Shaft Down**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**HP**	Overall Length	**37.61 in**
Frame Length	**14.5 in**	Shaft Diameter	**1 5/8 in**
Shaft Extension	**4.50 in**	Assembly/Box Mounting	**F1/F2 Capable**

Drawings

Connection Drawing	**EE7308K**	Outline Drawing	**B-SS518657-1450**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 15/10/2026



NOTES:
1. CONDUIT BOX CAN BE ROTATED IN 90° STEPS
2. NAMEPLATES TO BE READ FROM CONDUIT BOX SIDE OF MOTOR

(REPLACES B-SS507344)

DASH	FRAME	C	AG	BV
1450	360HPV	37.61	33.11	13.88

DRAWING REVISION G	REVISION BY SV	REV DATE/© DATE 05/27/2026
REQUEST NUMBER CR-0026396	APPROVED BY RMS	DATE 05/27/2026
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):


DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 INCH / 5.1 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY


DRAWN BY TJB	marathon™
DATE 08-10-2001	
APPROVED BY GK	DESCRIPTION: OUTLINE, 360HPV-TEFC-VERT. 'P' BASE
DATE 08-13-2001	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE B / DRAWING NUMBER SS518657 / SHEET 1 OF 1


Uncontrolled Copy

LOW VOLTAGE



HIGH VOLTAGE





VIEW OF TERMINAL END

DRAWING REVISION: F	REVISION BY: SB	REV DATE/ © DATE: 08/01/2025	DRAWN BY: PGK	marathon™
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025	DATE: 06/04/1997	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED			APPROVED BY: GK	DESCRIPTION: CONN DIAGRAM-EXTERNAL DELTA CON. - 3ø - 9 LEADS
			DATE: 06/15/1997	
			REFERENCE	MATERIAL / PROCESS/FINISH
			THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: EE7308K / SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED.
PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

Data Sheet

Date: 12/3/2018
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

365TTFS16013

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	22.5	30.0	46.0	64.0	84.0	96.0	106	542	
Torque (ft-lb)	0.00	27.5	55.0	83.0	111	128	140	180	
RPM	3600	3590	3580	3565	3555	3,545	3540	0	
Efficiency (%)		92.4	94.5	94.5	94.5	94.1	93.6		
P.F. (%)	6.0	63.0	81.0	86.5	88.5	89.0	89.0	31.5	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	1800	3350	3555	3600
Current (Amps)	542	488	335	84.0	22.5
Torque (ft-lb)	180	162	320	111	0.00



Information Block

HP	75.0	
Sync. RPM	3600	
Frame	365	
Enclosure	TEFC	
Construction	TFS	
Voltage	230/460	V
Frequency	60	Hz
Design	A	
LR Code letter	G	
Service Factor	1.15	
Temp Rise @ FL	80	° C
Duty	CONT	
Ambient	40	° C
Elevation	1,000	feet
Rotor/Shaft wk²	8.2	Lb-Ft²
Ref Wdg	T365262 NONE	
Sound Pressure @ 1M	75	dBA
VFD Rating	NONE	
Outline Dwg	B-SS518657-1450	
Conn. Diag	A-EE7308K	
Additional Specifications:		
0		
0		

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.0550	0.0410	0.3190	0.2800	11.3780

