marathon®

Explosion Proof Motors

Model No: 365TTGS16540
Catalog No: E576A

Explosion Proof Motor, 75 & 60 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 365T Frame, EPFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 365TTGS16540, Catalog No: E576A Explosion Proof Motor, 75 & 60 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 365T Frame, EPFC

Nameplate Specifications

Phase	**3**	Output HP	**75 & 60 Hp**
Output KW	**56.0 & 45.0 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1782 & 1482 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.00 & 1.00**	Frame	**365T**
Enclosure	**Explosion Proof Fan cooled**	Thermal Protection	**Thermostat**
Efficiency	**95.4 & 95 %**	Ambient Temperature	**50 °C**
Frequency	**60 & 50 Hz**	Current	**174/87 & 169/84.5 A**
Power Factor	**84**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**A**
KVA Code	**H**	Drive End Bearing Size	**6314**
Opp Drive End Bearing Size	**6312**	UL	**UL Listed And CSA Certified**
CSA	**Y**	CE	**N**
IP Code	**54**	Number of Speeds	**1**
Hazardous Location	**DIV 1 EXP PROOF CL I GR CD CL II GR FG T3C**		


Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.069 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**T**	Overall Length	**32.74 in**
Frame Length	**14.5 in**	Shaft Diameter	**2 3/8 in**
Shaft Extension	**6.12 in**	Assembly/Box Mounting	**F1 Only**
Inverter Load	**Constant 2:1/Variable 10:1**		


Drawings

Connection Drawing	**A-EE7308AD**	Outline Drawing	**B-SS518459-1450**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026







NOTES:
1. CONDUIT BOX CAN BE ROTATED IN 90° STEPS.
2. CONDUIT BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°.
3. NAMEPLATES TO BE READ FROM CONDUIT BOX SIDE OF MOTOR.

DASH	FRAME	B	C	2F	BS
1350	364T	13.25	31.74	11.25	5.62
1450	365T	14.25	32.74	12.25	6.12

DRAWING REVISION	REVISION BY	REV DATE/© DATE
H	SV	05/28/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026424	RMS	05/28/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 / 5.1 / INCH / mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	
TJB	
DATE	
05-14-2001	
APPROVED BY	
GK	
DATE	
09-07-2001	
REFERENCE	
THIRD ANGLE PROJECTION	


marathon™

DESCRIPTION
OUTLINE
360T FR. - EXP. PROOF


MATERIAL | PROCESS/FINISH


SIZE	DRAWING NUMBER	SHEET
B	SS518459	1 OF 1

LOW VOLTAGE




HIGH VOLTAGE







LOW VOLTAGE



HIGH VOLTAGE





VIEW OF TERMINAL END

WHEN MORE THAN ONE PROT. IS USED; PROT. ARE CONNECTED IN SERIES

DRAWING REVISION M	REVISION BY SB	REV DATE/© DATE 06/03/2026	PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY MJD	marathon™
REQUEST NUMBER CR-0026504	APPROVED BY RMS	DATE 06/03/2026		DATE 12-19-1997	
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED				APPROVED BY GK	DESCRIPTION CONN DIAGRAM-EXTERNAL
				DATE 01-07-1998	
				REFERENCE	MATERIAL / PROCESS/FINISH
				THIRD ANGLE PROJECTION	SIZE A / DRAWING NUMBER ee7308ad / SHEET 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

Uncontrolled Copy

Data Sheet

Date: 20-06-2017
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

365TTGS16540

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	32.0	38.0	51.5	68.5	87.0	99.0	108	650	
Torque (ft-lb)	0.00	55.0	110	166	221	255	278	500	
RPM	1800	1795	1790	1785	1782	1,778	1775	0	
Efficiency (%)		92.4	95.0	95.4	95.4	95.4	95.0		
P.F. (%)	3.5	50.0	72.0	81.0	84.0	85.0	85.5	33.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1725	1782	1800
Current (Amps)	650	575	360	87.0	32.0
Torque (ft-lb)	500	425	625	221	0.00



Information Block

HP	75.0
Sync. RPM	1800
Frame	365
Enclosure	TEFC
Construction	TFS
Voltage	230/460#190/38(V
Frequency	60 Hz
Design	A
LR Code letter	H
Service Factor	1.15
Temp Rise @ FL	75 ° C
Duty	CONT
Ambient	40 ° C
Elevation	1,000 feet
Rotor/Shaft wk²	18.5 Lb-Ft²
Ref Wdg	T3654203 NONE
Sound Pressure @ 1M	68 dBA
VFD Rating	CONSTANT 2:1
Outline Dwg	B-SS518459-1450
Conn. Diag	A-EE7308AD

Additional Specifications:


0

365THFS8036

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.0510	0.0330	0.2910	0.3550	8.1840

Speed -Torque Curve



Uncontrolled Copy

CERTIFICATION DATA SHEET

Model#:	365TTGS16540 AN	**WINDING#:**	T3654203 NONE 1
CONN. DIAGRAM:	A-EE7308AD	**ASSEMBLY:**	F1 ONLY
OUTLINE:	B-SS518459-1450		

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
75&60	56&45	1800	1782&1482	365T	EPFC	H	A

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	230/460#190/380	174/87&169/84.5	LINE OR INVERTER	CONTINUOUS	F3	1.15/1.15	40	3300

FULL LOAD EFF: 95.4&95	3/4 LOAD EFF: 95.4	1/2 LOAD EFF: 95	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 84&84	**3/4 LOAD PF: 81**	**1/2 LOAD PF: 72**	95	SQ CAGE INV RATED	64 / 32

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
221 LB-FT	1300 / 650	500 LB-FT 225	625 LB-FT 282	75

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
68 dBA	78 dBA	18.5 LB-FT^2	500 LB-FT^2	25 SEC.	2	1050 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	PREMIUM SEVERE DUTY	EXP PROOF CL I GR C&D CL II GR F&G T3B	FALSE	NONE	BLUE (EPOXY)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL 6314	BALL 6312	POLYREX EM	T	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
TSTATS (N/C)	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

INVERTER TORQUE: CONSTANT 2:1
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

*
N
O
T
E
S
*

DATE: 06/22/2017 03:33:49 AM
FORM 3531 REV.3 02/07/99
** Subject to change without notice.