

Crusher Duty Motors

Model No: 445TTFC6633

Catalog No: Y826B

Crusher Duty Motor, 150 & 125 HP, 3 Ph, 60 & 50 Hz, 460 & 380 V, 1800 RPM, 445T Frame, TEFC

Product Information Packet: Model No: 445TTFC6633, Catalog No: Y826B Crusher Duty Motor, 150 & 125 HP, 3 Ph, 60 & 50 Hz, 460 & 380 V, 1800 RPM, 445T Frame, TEFC

Nameplate Specifications


Phase	3	Output HP	150 & 125 Hp
Output KW	112.0 & 93.0 kW	Voltage	460 & 380 V
Speed	1786 & 1486 r/min	Synchronous RPM	1800 & 1500 r/min
Service Factor	1.15 & 1.15	Frame	445T
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	95.8 & 95 %	Ambient Temperature	40 °C
Frequency	60 & 50 Hz	Current	165 & 168 A
Power Factor	88	Duty	Continuous
Insulation Class	F	Design Code	C
KVA Code	G	Drive End Bearing Size	NU319
Opp Drive End Bearing Size	6317	UL	Recognized
CSA	Y	CE	Y
IP Code	55	Number of Speeds	1

Technical Specifications


Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Part Wdg Start & Wye Start Delta Run Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.03 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Roller
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Overall Length	50.78 in
Shaft Diameter	3 3/8 in	Shaft Extension	8.5 in
Assembly/Box Mounting	F1/F2 Capable	Inverter Load	Constant 10:1

Drawings

Connection Drawing	EE7300BH	Outline Drawing	SS620677-445T
--------------------	----------	-----------------	---------------



VIEW OF TERMINAL END



DRAWING REVISION E		REVISION BY SB		REV DATE/ © DATE 08/04/2025		DRAWN BY RJW		marathon™					
REQUEST NUMBER CR-0023654		APPROVED BY SBD		DATE 08/04/2025		DATE 02/11/2005							
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED						PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY		APPROVED BY GK		DESCRIPTION CONNECTION DIAGRAM			
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. (OWNER) AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.								DATE 02/11/2005		12 LEAD - SINGLE VOLTAGE			
								REFERENCE		MATERIAL		PROCESS/FINISH	
								THIRD ANGLE PROJECTION				SIZE A	DRAWING NUMBER EE7300BH

Data Sheet

Date: 29-06-2017

Customer:

Attention:

Submitted by: FAREEDA DUDEKULA



445TFC6633

Submittal

Data @ 460 V

Motor Load Data


Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	40.0	57.0	88.0	125	165	192	210	1,085	
Torque (ft-lb)	0.00	110	220	330	441	508	553	975	
RPM	1800	1796	1792	1790	1786	1,782	1780	0	
Efficiency (%)		93.6	95.4	95.8	95.8	95.8	95.4		
P.F. (%)	6.0	67.0	83.0	87.0	88.0	88.0	88.0	36.0	

Motor Speed Data


	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1725	1786	1800
Current (Amps)	1,085	950	550	165	40.0
Torque (ft-lb)	975	775	1,050	441	0.00

Information Block

HP	150.0			
Sync. RPM	1800			
Frame	445			
Enclosure	TEFC			
Construction	TFC			
Voltage	460#380 V			
Frequency	60 Hz			
Design	A			
LR Code letter	G			
Service Factor	1.15			
Temp Rise @ FL	60 ° C			
Duty	CONT			
Ambient	40 ° C			
Elevation	1,000 feet			
Rotor/Shaft wk ²	75.0 Lb-Ft ²			
Ref Wdg	CHT44540006 NONE			
Sound Pressure @ 1M	75 dBA			
VFD Rating	CONSTANT 10:1			
Outline Dwg	SS620677			
Conn. Diag	EE7300BH			
Additional Specifications:				
0				
365THFS8036				
EQUIV CKT (OHMS / PHASE)				
R1	R2	X1	X2	Xm
0.0230	0.0130	0.1270	0.2630	6.5670



Speed -Torque Curve



CERTIFICATION DATA SHEET

Model#: 445TTFC6633 AA
 CONN. DIAGRAM: EE7300BH
 OUTLINE: SS620677

WINDING#: CHT44540006 NONE 1
 ASSEMBLY: F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
150&125	112&93	1800	1786&1486	445T	TEFC	G	C

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	460#380	165&168	PWS & YDRUN OR INV	CONTINUOU S	F7	1.15/1.15	40	3300

FULL LOAD EFF: 95.8&95	3/4 LOAD EFF: 95.8	1/2 LOAD EFF: 95.4	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 88&88	3/4 LOAD PF: 87	1/2 LOAD PF: 83	95	SQ CAGE INV RATED	40

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
441 LB-FT	1085	975 LB-FT 220	1050 LB-FT 238	80

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
75 dBA	85 dBA	75 LB-FT^2	1000 LB-FT^2	25 SEC.	2	3050 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	PREMIUM SEVERE DUTY	NONE	FALSE	NONE	BLUE (EPOXY)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
ROLLER	BALL	SHC- 100/POLYREX	T	NONE	NONE	4140 STRESSPROOF (C-214)	CAST IRON
NU319	6317						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

* N O T E S *	INVERTER TORQUE: CONSTANT 10:1 INV. HP SPEED RANGE: NONE					
	ENCODER: NONE NONE NONE NONE NONE PPR					
	BRAKE: NONE NONE NONE P/N NONE NONE NONE NONE FT-LB NONE V NONE Hz					

DATE: 06/21/2017 05:48:31 AM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.

