

Fire Pump Motors

Model No: 449TSTFS14044

Catalog No: Y1647

Fire Pump Motor, 350 & 300 HP, 3 Ph, 60 & 50 Hz, 460 & 380 V, 1800 RPM, 449TS Frame, TEFC

Product Information Packet: Model No: 449TSTFS14044, Catalog No: Y1647 Fire Pump Motor, 350 & 300 HP, 3 Ph, 60 & 50 Hz, 460 & 380 V, 1800 RPM, 449TS Frame, TEFC

Nameplate Specifications


Phase	3	Output HP	350 & 300 Hp
Output KW	260.0 & 224.0 kW	Voltage	460 & 380 V
Speed	1785 & 1485 r/min	Synchronous RPM	1800 & 1500 r/min
Service Factor	1.15 & 1.15	Frame	449TS
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	95.4 & 95 %	Ambient Temperature	40 °C
Frequency	60 & 50 Hz	Current	400 & 415 A
Power Factor	86	Duty	Continuous
Insulation Class	F	Design Code	B
KVA Code	G	Drive End Bearing Size	6319
Opp Drive End Bearing Size	6319	UL	No
CSA	Y	CE	Y
IP Code	43	Number of Speeds	1


Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Part Wdg Start & Wye Start Delta Run
Poles	4	Rotation	Reversible
Resistance Main	.007 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	TS	Overall Length	48.11 in
Frame Length	28.75 in	Shaft Diameter	2 3/8 in
Shaft Extension	5 in	Assembly/Box Mounting	F1/F2 Capable


Drawings

Connection Drawing	EE7300BH	Outline Drawing	SS559506-2875
--------------------	----------	-----------------	---------------





VIEW OF TERMINAL END



DRAWING REVISION E		REVISION BY SB		REV DATE/ © DATE 08/04/2025		DRAWN BY RJW		<div>marathon™</div>					
REQUEST NUMBER CR-0023654		APPROVED BY SBD		DATE 08/04/2025		DATE 02/11/2025							
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED						PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY		APPROVED BY GK		DESCRIPTION CONNECTION DIAGRAM			
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. (OWNER) AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.								DATE 02/11/2025		12 LEAD - SINGLE VOLTAGE			
								REFERENCE		MATERIAL		PROCESS/FINISH	
								THIRD ANGLE PROJECTION				SIZE A	DRAWING NUMBER EE7300BH

Data Sheet

Date: 6/19/2017

Customer: _____

Attention: _____

Submitted by: FAREEDA DUDEKULA



449TSTFS14045

Submittal

Data @ 460 V


Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	92.0	124	185	258	335	382	420	2,150	
Torque (ft-lb)	0.00	219	439	660	882	1,015	1,105	1,600	
RPM	1800	1796	1794	1790	1788	1,785	1782	0	
Efficiency (%)		90.2	94.1	95.4	95.4	95.4	95.0		
P.F. (%)	7.0	63.0	80.0	86.0	87.0	87.0	87.0	28.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle																																	
Speed (RPM)	0	900	1725	1788	1800																																	
Current (Amps)	2,150	2,050	1,150	335	92.0																																	
Torque (ft-lb)	1,600	1,450	2,100	882	0.00																																	
<div><div>— Efficiency (%) — P.F. (%) — Current (Amps)</div><table><caption>Graph Data Points (Estimated)</caption><thead><tr><th>Load (%)</th><th>Efficiency (%)</th><th>P.F. (%)</th><th>Current (Amps)</th></tr></thead><tbody><tr><td>0</td><td>-</td><td>-</td><td>100</td></tr><tr><td>25</td><td>90</td><td>63</td><td>120</td></tr><tr><td>50</td><td>93</td><td>78</td><td>160</td></tr><tr><td>75</td><td>94</td><td>85</td><td>230</td></tr><tr><td>100</td><td>95</td><td>87</td><td>300</td></tr><tr><td>125</td><td>95</td><td>87</td><td>420</td></tr></tbody></table></div>						Load (%)	Efficiency (%)	P.F. (%)	Current (Amps)	0	-	-	100	25	90	63	120	50	93	78	160	75	94	85	230	100	95	87	300	125	95	87	420					
						Load (%)	Efficiency (%)	P.F. (%)	Current (Amps)																													
						0	-	-	100																													
						25	90	63	120																													
						50	93	78	160																													
						75	94	85	230																													
						100	95	87	300																													
						125	95	87	420																													
						HP		300.0																														
						Sync. RPM		1800																														
						Frame		449																														
						Enclosure		TEFC																														
						Construction		TFN																														
						Voltage		460#380 V																														
						Frequency		60 Hz																														
						Design		A																														
						LR Code letter		G																														
Service Factor		1.15																																				
Temp Rise @ FL		80 ° C																																				
Duty		CONT																																				
Ambient		40 ° C																																				
Elevation		1,000 feet																																				
Rotor/Shaft wk²		92.0 Lb-Ft²																																				
Ref Wdg		T4494191 NONE																																				
Sound Pressure @ 1M		85 dBA																																				
VFD Rating		NONE																																				
Outline Dwg		B-SS515643-2875																																				
Conn. Diag		A-EE7300BH																																				
Additional Specifications:																																						
0																																						
0																																						
EQUIV CKT (OHMS / PHASE)																																						
R1		R2		X1		X2		Xm																														
0.0080		0.0060		0.0720		0.1150		2.9010																														

Speed -Torque Curve



CERTIFICATION DATA SHEET

Model#: 449TSTFS14044 AA
 CONN. DIAGRAM: A-EE7300BH
 OUTLINE: B-SS515643-2875

WINDING#: T449436 NONE 2
 ASSEMBLY: F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
350&300	260&224	1800	1785&1485	447/449TS	TEFC	G	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	460#380	400&415	PWS & YDRUN	CONTINUOUS	F1	1.15/1.15	40	3300

FULL LOAD EFF: 95.4&95	3/4 LOAD EFF: 95.4	1/2 LOAD EFF: 94.5	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 86&86	3/4 LOAD PF: 83.5	1/2 LOAD PF: 77	94.5	SQ CAGE IND RUN	122

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
1030 LB-FT	2500	1975 LB-FT 192	2550 LB-FT 248	80

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
85 dBA	95 dBA	95 LB-FT^2	2225 LB-FT^2	25 SEC.	1	3050 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	RED (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL	BALL						
6318	6316	POLYREX EM	TS	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

* N O T E S *	INVERTER TORQUE: NONE		
	INV. HP SPEED RANGE: NONE		
	ENCODER: NONE		
	NONE NONE		
	NONE NONE PPR		
	BRAKE: NONE NONE		
	NONE P/N NONE		
	NONE NONE		
	- FT-LB	NONE V	NONE Hz

DATE: 06/21/2017 06:51:46 AM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.