marathon®

General Purpose Motors

Model No: LM16769
Catalog No: LM16769

General Purpose Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 380-415 V, 1200 RPM, 286TC Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: LM16769, Catalog No: LM16769 General Purpose Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 380-415 V, 1200 RPM, 286TC Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**20 & 15 Hp**
Output KW	**14.9 & 11.2 kW**	Voltage	**230/460 & 380-415 V**
Speed	**1182 & 984 r/min**	Synchronous RPM	**1200 & 1000 r/min**
Service Factor	**1.15 & 1.00**	Frame	**286TC**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**91.7 & 91 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**61/30.5 & 27.5-28.5 A**
Power Factor	**66.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**F**	Drive End Bearing Size	**6312**
Opp Drive End Bearing Size	**6209**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Wye Start Delta Run**
Poles	**6**	Rotation	**Reversible**
Resistance Main	**.3499 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Aluminum**
Shaft Type	**T**	Overall Length	**28.01 in**
Frame Length	**15.25 in**	Shaft Diameter	**1 7/8 in**
Shaft Extension	**4.38 in**	Assembly/Box Mounting	**F1/F2 Capable**


Drawings

Connection Drawing	**EE7358**	Outline Drawing	**XF5F1SC1-1525**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

Uncontrolled Copy





F2 VIEW

NOTES:
1. CONDUIT BOX CAN BE ROTATED IN 90° STEPS.
2. CONDUIT BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°.
3. NAMEPLATE TO BE READ FROM CONDUIT BOX SIDE OF MOTOR.

DASH	FRAME	C	B	AG	2F	2FF	2FFF	BS
1375	284TC	26.02	13.88	21.64	9.50			1.69
1525	286TC	27.52	15.38	23.14	11.00	9.50	9.50	1.69

DRAWING REVISION: J	REVISION BY: SB	REV DATE/ © DATE: 11/13/2025
REQUEST NUMBER: CR-0024625	APPROVED BY: RMS	DATE: 11/13/2025
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		

COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.
PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	± 0.1	± 3)	± 0.5 °
.XX	± 0.01	[± 0.3]	
.XXX	± 0.005	[± 0.13]	
.XXXX	± 0.0005	[± 0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45 °
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 125 INCH / 3.2 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	TJB
DATE	06-11-2002
APPROVED BY	TB
DATE	06-14-2002
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION: OUTLINE
280TC TEFC UEI

MATERIAL | PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
B	XF5F1SC1	1 OF 1