marathon®

# General Purpose Motors

**Model No:** TCA0551AE211GAA009
**Catalog No:** R503A

General Purpose Motor, 75 & 60 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V, 3600 RPM, 250M Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

## Product Information Packet: Model No: TCA0551AE211GAA009, Catalog No: R503A General Purpose Motor, 75 & 60 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V, 3600 RPM, 250M Frame, TEFC

### Nameplate Specifications

| | | | |
|---|---|---|---|
| Phase | **3** | Output HP | **75 & 60 Hp** |
| Output KW | **55.0 & 45.0 kW** | Voltage | **230/460 & 200/400 V** |
| Speed | **3575 & 2980 r/min** | Synchronous RPM | **3600 & 3000 r/min** |
| Service Factor | **1.15** | Frame | **250M** |
| Enclosure | **Totally Enclosed Fan Cooled** | Thermal Protection | **No Protection** |
| Efficiency | **93.6 & 94 %** | Ambient Temperature | **40 °C** |
| Frequency | **60 & 50 Hz** | Current | **171.4/85.7 & 166/83 A** |
| Power Factor | **89** | Duty | **Continuous** |
| Insulation Class | **F8** | Design Code | **N (IEC)** |
| KVA Code | **F** | Drive End Bearing Size | **6314** |
| Opp Drive End Bearing Size | **6314** | UL | **Recognized** |
| CSA | **N** | CE | **Y** |
| IP Code | **55** | Number of Speeds | **1** |

### Technical Specifications

| | | | |
|---|---|---|---|
| Electrical Type | **Squirrel Cage Inverter Rated** | Starting Method | **Line Or Inverter** |
| Poles | **2** | Rotation | **Reversible** |
| Resistance Main | **.11 O** | Mounting | **B3** |
| Motor Orientation | **Horizontal** | Drive End Bearing | **Ball** |
| Opp Drive End Bearing | **Ball** | Frame Material | **Cast Iron** |
| Shaft Type | **IEC** | Overall Length | **37.05 in** |
| Frame Length | **18.11 in** | Shaft Diameter | **2.559 in** |
| Shaft Extension | **5.51 in** | Assembly/Box Mounting | **F3** |
| Inverter Load | **Constant 2:1/Variable 10:1** | | |

### Drawings


| | | | |
|---|---|---|---|
| Connection Drawing | **8442000715** | Outline Drawing | **SS557723** |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

| DRAWING REVISION | REVISION BY | REV DATE/© DATE |
|---|---|---|
| B | SB | 08/01/2025 |
| REQUEST NUMBER | APPROVED BY | DATE |
| CR-0023654 | SBD | 08/01/2025 |
| REQUEST NUMBER DESCRIPTION | | |
| DRAWING TITLE BLOCK UPDATED | | |

| GEOMENTRIC TOLERANCE | | |
|---|---|---|
| LINEAR DIM | >0~6 | ±0.1 |
| | >6~30 | ±0.2 |
| | >30~120 | ±0.3 |




NOTES:

1. PRESSURE-SENSITIVE ADHESIVE COATED PAPER ON THE BACK OF SELF-ADHESIVE.
2. AT THE END OF YELLOW, WORDS, SYMBOLS, LETTERS ARE BLACK, BORDER IS BLACK.
3. THE TOLERANCE OF THE LINEAR SIZE OF THE TOLERANCE WITHOUT THE TOLERANCE BY THE TABLE.
4. LEAD TERMINAL MARKINGS FONT SIZE : T1-T12 & U1-U4,V1-V4& W1-W4 OF ARIAL WITH 3mm SIZE
5. OTHER LETTER FONT SIZE SHOULD BE 3.5mm.

8WD.442.2017

| | | | |
|---|---|---|---|
| PRIMARY DIMENSIONS ARE mm<br>INCH DIMENSIONS IN [BRACKETS]<br>ARE FOR REFERENCE ONLY | DRAWN BY: S.MUDDA<br>DATE: 16/11/2020<br>APPROVED BY: SUMANTA<br>DATE: 16/11/2020<br>REFERENCE | marathon™<br>DESCRIPTION: CONN DIAGRAM-NAMEPLATE<br>MATERIAL | PROCESS/FINISH |
| THIRD ANGLE PROJECTION | SIZE: A | DRAWING NUMBER: 8442000715 | SHEET: 1 OF 1 |