marathon®

General Purpose Motors

Model No: TCA7P53AP211GAA009
Catalog No: R432

General Purpose Motor, 10 HP, 3 Ph, 60 Hz, 575 V, 1200 RPM, 160M Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: TCA7P53AP211GAA009, Catalog No: R432 General Purpose Motor, 10 HP, 3 Ph, 60 Hz, 575 V, 1200 RPM, 160M Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**10 Hp**
Output KW	**7.5 kW**	Voltage	**575 V**
Speed	**1180 r/min**	Service Factor	**1.00**
Frame	**160M**	Enclosure	**Totally Enclosed Fan Cooled**
Thermal Protection	**No Protection**	Efficiency	**91 %**
Ambient Temperature	**40 °C**	Frequency	**60 Hz**
Current	**12.1 A**	Power Factor	**78**
Duty	**Continuous**	Insulation Class	**F8**
Design Code	**N (IEC)**	KVA Code	**G**
Drive End Bearing Size	**6309**	Opp Drive End Bearing Size	**6209**
UL	**Recognized**	CSA	**N**
CE	**Y**	IP Code	**55**

Technical Specifications

Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**6**	Rotation	**Selective Clockwise**
Resistance Main	**1.19 O**	Mounting	**B3**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**IEC**	Assembly/Box Mounting	**F3**

Drawings


Connection Drawing	**8442000700**	Outline Drawing	**SS208563**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

DRAWING REVISION	REVISION BY	REV DATE/© DATE
B	SV	05/11/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026249	RMS	05/11/2026
REQUEST NUMBER DESCRIPTION		
DRAWING TITLE BLOCK UPDATED		

GEOMENTRIC TOLERANCE		
LINEAR DIM	>0~6	±0.1
	>6~30	±0.2
	>30~120	±0.3



NOTES:

1. PRESSURE-SENSITIVE ADHESIVE COATED PAPER ON THE BACK OF SELF-ADHESIVE.
2. AT THE END OF YELLOW, WORDS, SYMBOLS, LETTERS ARE BLACK, BORDER IS BLACK.
3. THE TOLERANCE OF THE LINEAR SIZE OF THE TOLERANCE WITHOUT THE TOLERANCE BY THE TABLE.

PRIMARY DIMENSIONS ARE mm INCH DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY: DNB DATE: 16/12/2016 APPROVED BY: JAY DATE: 16/06/2020 REFERENCE THIRD ANGLE PROJECTION	marathon™ DESCRIPTION: CONN DIAGRAM-NAMEPLATE 3 LEAD MATERIAL / PROCESS/FINISH SIZE: A DRAWING NUMBER: 8442000700 SHEET: 1 OF 1